

# Product data sheet

Specifications



## panel GLASS TOUCH PANELS for hotels - modbus - 3 buttons - sample order

LSSMBU03NS

### Main

|                               |                                                                                                                                                                                |
|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Name                  | Glass Touch Panels                                                                                                                                                             |
| Product Type                  | Configurable touchscreen panel                                                                                                                                                 |
| Device Application            | Monitoring<br>Ventilation<br>Lighting<br>Energy efficiency<br>Bell switch<br>Remote control<br>Hotel                                                                           |
| Color Buttons Display Options | Black<br>Silver<br>Champagne gold<br>White                                                                                                                                     |
| Colour Tint                   | Panel: black<br>Panel: white<br>Panel: silver<br>Panel: champagne gold<br>Button: white<br>Button: amber<br>Button: blue<br>Button: light green<br>Button: red<br>Button: grey |
| Module Configuration          | Configured with the Glass Touch Panel Design tool                                                                                                                              |

### Complementary

|                             |                                       |
|-----------------------------|---------------------------------------|
| Control Button Type         | 3 configurable touch button           |
| Local Signalling            | configurable                          |
| [Us] Rated Supply Voltage   | 24 V DC                               |
| Current Consumption         | 30 mA                                 |
| Communication Port Protocol | Modbus serial with RS485 port(s)      |
| Mounting Mode               | Snap-in<br>Magnetic                   |
| Height                      | 105 mm (standard)<br>95 mm (optional) |
| Width                       | 105 mm (standard)<br>95 mm (optional) |
| Depth                       | 33 mm (standard)<br>33 mm (optional)  |
| Relative Humidity           | 10...95 %, non-condensing (operation) |
| Order Type                  | Mockup sample order                   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Environment

|                                       |           |
|---------------------------------------|-----------|
| Ambient Air Temperature For Storage   | 0...60 °C |
| Ambient Air Temperature For Operation | 0...45 °C |

# Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 5.5 cm   |
| Package 1 Width              | 13.5 cm  |
| Package 1 Length             | 18.5 cm  |
| Package 1 Weight             | 300.0 g  |
| Unit Type Of Package 2       | S03      |
| Number Of Units In Package 2 | 20       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 7.0 kg   |
| Unit Type Of Package 3       | P12      |
| Number Of Units In Package 3 | 480      |
| Package 3 Height             | 105.0 cm |
| Package 3 Width              | 80.0 cm  |
| Package 3 Length             | 120.0 cm |
| Package 3 Weight             | 183.0 kg |