

Product data sheet

Specifications



Climasys Ultra thin resistance heater low starting current 12W 120V 110x140mm

NSYCRS10W120V

⚠ Discontinued on: Dec 31, 2021

⚠ Discontinued

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	12 W
Input Voltage	120 V AC 50/60 Hz
Electrical Connection	Cable length: 2 m

Complementary

Operating Position	Vertical Horizontal
Ambient Air Temperature For Operation	-60...70 °C
Temperature Setting Range	-40...70 °C
Material	Silicone rubber
Height	110 mm external:
Width	140 mm external:
Depth	1.6 mm external:
Device Composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts fixing accessories
Condition Of Use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing Mode	By 4 screws
Mounting Support	DIN rail Standard mounting plate Adhesive Velcro Telequick mounting plate

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✓</div><div>Reach Free Of Svhc</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
<div>Eu Rohs Directive</div>	<div><div>Compliant</div><div>EU RoHS Declaration</div></div>
<div>China Rohs Regulation</div>	<div><div>China RoHS declaration</div><div>Product out of China RoHS scope. Substance declaration for your information</div></div>
<div>Weee</div>	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</div>