

# Product data sheet

Specifications



## ClimaSys standard cooling unit roof of enclosure - 820W at 230 V

NSYCU800RUL

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

### Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Cooling unit
Mounting Type	Roof of enclosure
Installation	Indoor roof
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	230 V AC at 50/60 Hz, 1 phase
Rated Power	800 W
Cooling Power	2800 Btu/h 50/60 Hz L35-L35 2320 Btu/h 50/60 Hz L35-L50

### Complementary

Height	340 mm
Width	600 mm
Depth	340 mm
[In] Rated Current	2.9 A
Inrush Current	12 A
Power Consumption In W	510 W at 50/60 Hz, L35-L35 560 W at 50/60 Hz, L35-L50
Energy Efficiency Ratio	1.6
Control Type	Electronic controller
Temperature Setting Range	20...50 °C
Ambient Air Temperature For Operation	50 °C maximum: 20...46 °C inside the enclosure: 20...50 °C outside the enclosure:
Noise Level	65 dB
Pressure	25 bar
Flow Rate	Internal circuit: 570 m3/h at 50/60 Hz External circuit: 860 m3/h at 50/60 Hz
Net Weight	23 kg
Cooling Gas Type	R134a (0.31 kg)
Type Of Filter	Optional external circuit filter

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):
Material	Steel
Colour	Grey (RAL 7035)

## Environment

Product Certifications	UL
Standards	DIN 3168
Ip Degree Of Protection	IP34 conforming to IEC 60529 (on the external circuit) IP54 conforming to IEC 60529 (on the internal circuit)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43.18 cm
Package 1 Width	40.64 cm
Package 1 Length	66.04 cm
Package 1 Weight	20.602 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	143.5 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	252.6 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>