

# Product data sheet

Specifications



Modular chassis DLM type for  
SPACIAL WM enclosure, 66  
modules, H700xW500mm.

NSYDLM66

## Main

|                                    |  |
|------------------------------------|--|
| Range                              | Spacial  |
| Accessory / Separate Part Category | Mounting accessory   |
| Application                        | Multi-purpose<br>Modular distribution application  |
| Product Or Component Type          | Chassis  |
| Device Short Name                  | DLM  |
| For Enclosure Nominal Dimensions   | -  |
| Mounting Location                  | Front of enclosure<br>Step slide   |
| Range Compatibility                | Spacial Spacial S3D<br>Spacial Spacial S3X<br>Spacial Spacial CRN  |
| Device Composition                 | 1 chassis structure<br>2 finish cover<br>1 neutral/earth strip 2 x 16 mm <sup>2</sup> 5 x 6 mm <sup>2</sup><br>3 front panels with 35 mm DIN rail<br>1 plain front panel with mounting plate |
| Quantity Per Set                   | Set of 1   |

## Complementary

|                               |  |
|-------------------------------|--|
| Material                      | Steel  |
| Colour                        | Front panel: grey (RAL 7035)                                 |
| Surface Finish                | Polyester powder   |
| Fixing Mode                   | By fixing element - on front and back with supports location |
| Adjustment                    | In height from 40 to 85 mm for DIN rail                      |
| Number Of Horizontal Rows     | 3  |
| Total Number Of 18 Mm Modules | 66   |
| Type Of Front Plate           | Plain and cut-out plates                                     |
| Number Of Cut-Out             | 3 cut-outs   |
| Height                        | 653 mm   |
| Width                         | 455 mm   |
| Depth                         | 101.5 mm   |

## Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |            |
|------------------------------|------------|
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 11.500 cm  |
| Package 1 Width              | 47.000 cm  |
| Package 1 Length             | 68.500 cm  |
| Package 1 Weight             | 6.438 kg   |
| Unit Type Of Package 2       | P12        |
| Number Of Units In Package 2 | 8          |
| Package 2 Height             | 90.000 cm  |
| Package 2 Width              | 80.000 cm  |
| Package 2 Length             | 120.000 cm |
| Package 2 Weight             | 63.504 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |