

Product data sheet

Specifications



Fluorescent lamp type T5 -14W, 220V, 21W total power

NSYLAM14T5

ⓘ Discontinued

Main

Range Of Product	Lighting and power sockets
Accessory / Separate Part Category	Lighting accessory
Product Or Component Type	Lamp
Device Application	Multi-purpose
Device Composition	fixing elements interconnection cable lamp

Complementary

Rated Lamp Wattage	14 W
[Ue] Rated Operational Voltage	220 V 50/60 Hz
Bulb Base	T5
Bulb Type	Fluorescent
Luminous Flux	650 lm
Service Life In Hours	8000 h
Electrical Connection	1 pre-cabled male connector Cable 3 m
Mounting Location	Top front of enclosure
Mounting Support	Upright DIN rail Metal parts Cross rails
Fixing Mode	Magnetic fixing Screws
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Thalassa Thalassa PLA Thalassa Thalassa PLM Spacial Spacial SFX Spacial Spacial SMX Spacial Spacial SF Spacial Spacial SM
Material	White plastic
Height	20 mm
Width	575 mm
Depth	36 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class II
Flame Retardance	V0 conforming to UL 94
Electromagnetic Compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4
Standards	UL 508 A
Ambient Air Temperature For Operation	-16...65 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------