

Product data sheet

Specifications



trip unit MicroLogic 2.2 M for
ComPact NSX 100/160/250 circuit
breakers, electronic, rating 50 A, 3
poles 3d

LV429172

! Discontinued

! Discontinued on: Dec 25, 2023

Important message: This product has been switched to new
ComPacT range and is no longer commercialized.

Main

Range	ComPact
Range Of Product	ComPact NSX100...250
Product Or Component Type	Trip unit
Trip Unit Name	MicroLogic 2.2 M
Trip Unit Technology	Electronic
Range Compatibility	ComPact NSX100 ComPact NSX160 ComPact NSX250
Device Application	Motor
Number Of Poles	3P
Protected Poles Description	3t
Trip Unit Protection Functions	LSol
Protection Type	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
Trip Unit Rated Current	50 A at 65 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz

Complementary

Motor Tripping Class	20 5 10
Complementary Motor Protection	Phase unbalance
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	25...50 A
Long-Time Protection Delay Adjustment Type Tr	Fixed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Tr] Long-Time Protection Delay Adjustment Range	120 s at 1.5 x Ir for trip class 5 6.5 s at 6 x Ir for trip class 5 5 s at 7.2 x Ir for trip class 5 240 s at 1.5 x Ir for trip class 10 13.5 s at 6 x Ir for trip class 10 10 s at 7.2 x Ir for trip class 10 480 s at 1.5 x Ir for trip class 20 26 s at 6 x Ir for trip class 20 20 s at 7.2 x Ir for trip class 20
Thermal Memory	20 minutes before and after tripping
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick-Up Adjustment Range	5...13 x Ir
Short-Time Protection Delay Adjustment Type Tsd	Fixed
[Tsd] Short-Time Protection Delay Adjustment Range	0.01 s
Instantaneous Protection Pick-Up Adjustment Type Ii	Fixed
[Ii] Instantaneous Protection Pick-Up Adjustment Range	750 A
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	Without
Local Signalling	Flashing LED (green) for ready to operate LED 95 % Ith (red) for temperature over set point

Environment

Standards	UL 508 EN/IEC 60947-2
Product Certifications	Marine CCC
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	9.6 cm
Package 1 Length	11.2 cm
Package 1 Weight	439.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	28
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.711 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov