

Product data sheet

Specifications



Floor standing polyester enclosure,
Thalassa PLA, plain door, ventilated
canopy, 750x1250x420mm, IP44,
IK10

NSYPLAT7124G

Main

| | |
|---------------------------|--|
| Range | Thalassa |
| Product Name | Thalassa PLA |
| Enclosure Type | Multi-purpose |
| Product Or Component Type | Suitable enclosure |
| Version | PLAT |
| Nominal Height | 750 mm |
| Nominal Width | 1250 mm |
| Nominal Depth | 420 mm |
| Enclosure Mounting | Floor-standing |
| Device Composition | 1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy |

Complementary

| | |
|-----------------------------|--|
| Body Type | Open top and sealed bottom part assembled with side parts |
| Door Type | Plain front |
| Number Of Doors | 2 door(s) |
| Door Opening Side | Right and left (120 °) |
| Lock Type | 2 points handle lock, 5 mm double-bar |
| Accessibility For Operation | Top Rear Front |
| Removable Parts | Door by hinges Rear panel by fixing element Canopy by fixing element |
| Material | Polyester reinforced with fibreglass |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | Veritas |
| Electrical Insulation Class | Class II |

Environment

| | |
|-------------------------|---|
| Ip Degree Of Protection | IP44 conforming to IEC 60529 (with ventilated canopy) |
|-------------------------|---|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|--|---|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 (plain door) |
| Fire Resistance | 960 °C conforming to IEC 62208 |
| Ambient Air Temperature For Storage | -35...90 °C |

Packing Units

| | |
|-------------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 76.0 cm |
| Package 1 Width | 128.0 cm |
| Package 1 Length | 48.0 cm |
| Package 1 Weight | 46.334 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations