

Product data sheet

Specifications



Thalassa PHD - Set of 4 lifting eyes M12. Maximum load: 500kg

NSYPLHD

Main

Area	Thalassa
Category	Lifting accessory
Product Or Component Type	Lifting eye
Application	Multi-purpose
Mounting Location	Enclosure top
Range Compatibility	Thalassa Thalassa PHD
Device Composition	4 eyebolt
Quantity Per Set	Set of 1

Complementary

Material	Steel
Surface Finish	Zinc coated
Fixing Mode	Screwed - screw type M12
Permanent Permissible Load	500 kg
Height	3 mm
Width	200 mm
Depth	200 mm
Diameter	32 mm
Iso Thread	M12

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	20.0 cm
Package 1 Length	20.0 cm
Package 1 Weight	300.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	40 cm
Package 2 Width	30 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	20 cm
Package 2 Weight	6 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations