

Product data sheet

Specifications

Spacial SF/SM 180° pneumatic door stop for 19" swing rack - 180°



NSYRCDR18

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Mechanical retainer
Application	Electronic application Multi-purpose
For Enclosure Nominal Dimensions	- D: 600 mm - D: 800 mm - D: 1000 mm
Mounting Support	19" swing rack supports
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	fixing elements 1 pneumatic retainer
Quantity Per Set	Set of 1

Complementary

Fixing Mode	By fixing element: 19" swing rack support By fixing element: structure of enclosure
Operating Angle	180 °
Height	108 mm
Width	80 mm
Depth	570 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.8 cm
Package 1 Width	8.0 cm
Package 1 Length	57.0 cm
Package 1 Weight	510.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations