

Product data sheet

Specifications



Set of 4 step slides made of treated steel, D400mm

NSYSDCR400

Main

Category	Mounting accessory
Product Or Component Type	Step slide
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3CM
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Mounting Location	Sides of enclosure
Device Composition	4 sliding rails 4 sliding support fixing elements
Quantity Per Set	Set of 1
Material	Galvanised steel

Complementary

Fixing Mode	By fixing element On backstuds (welded in the enclosure)
Adjustment	In depth of the plate or other accessories in steps of 12.5 mm
Depth	400 mm nominal:
Net Weight	0.87 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	13.500 cm
Package 1 Length	37.000 cm
Package 1 Weight	1.120 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.624 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	104.992 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations