

Product data sheet

Specifications



Modular stainless console 304L,
Scotch Brite® finishing, W600xD200
mm.

NSYSDCX43

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Spacial
Accessory / Separate Part Category	Interface accessory
Product Or Component Type	Modular consoles
Anwendung	Multi-purpose
Nennmaße Des Gehäuses	-
Mounting Location	Top of control desk
Mounting Support	Direct fixing
Range Compatibility	Spacial Spacial SDX
Device Composition	1 door 1 body 1 lock 1 rear panel 4 step slides 1 door retainer
Quantity Per Set	Set of 1

Complementary

Material	Stainless steel 304L
Surface Finish	Scotch-Brite® brushed
Lock Type	Lock 3 mm double bar
Fixing Mode	By fixing element
Operating Angle	75 °
Height	483 mm
Width	Nominal: 400 mm
Depth	Nominal : 300 mm Maximum : 361 mm

Environment

Ip Degree Of Protection	IP55
Ik Degree Of Protection	IK10
Net Weight	15 kg

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	38.0 cm
Package 1 Width	41.5 cm
Package 1 Length	61.0 cm
Package 1 Weight	15.0 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	8
Package 2 Height	128.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	135.96 kg

Contractual warranty

Warranty	18 months
----------	-----------