


# Product data sheet

Specifications



Plug-in bridge, Linergy TR, 2 points,  
for mini spring terminals  
NSYTRR24M, 2 way, grey, set of 10

NSYTRALM22

 **Discontinued on:** Aug 31, 2023

 **Discontinued**

## Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Plug-in bridge
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRR spring terminal - passthrough terminal block, length = 32 mm
Number Of Ways	2 ways

## Complementary

Cable Cross Section	2.5 mm²
Number Of Connections	4
Number Of Measurement Input	0
Quantity Per Set	Set of 10
Net Weight	1.6 g
Colour	Red

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	4.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	0.900 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.000 cm
Package 2 Width	4.000 cm
Package 2 Length	9.000 cm
Package 2 Weight	10.000 g
Unit Type Of Package 3	S01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	270.000 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations