

Product data sheet

Specifications



2 Socket-outlet, New Unica, complete socket-outlet, 2P, 16A, European, with shutter, IP4X, glossy, untreated, white

NU206318

Main

Range	New Unica
Product Or Component Type	Socket-outlet
Aesthetic Name	Unica Studio
Device Presentation	Complete socket-outlet
Device Mounting	Flush
Socket Number	2
Outlet Poles Configuration	2P
Outlet Standard	European
Rated Current	16 A

Complementary

Device Application	Power supply
Cover Type	With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Fixing Mode	Screws
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals
Cable Cross Section	0...2.5 mm² cable(s), 2 - cable stiffness: flexible 0...2.5 mm² cable(s), 2 - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	PC: mechanism cover
Surface Finish	Glossy
Quantity Per Set	Set of 1 flow-pack
Standards	IEC 60884-1 UNE 20315-1-1 UNE 20315-1-2 NF C 61-314

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	AENOR EAC NF
Embedding Depth	24 mm
Depth	47 mm
Width	85 mm
Height	125 mm
Net Weight	0.099 kg
Surface Treatment	Untreated
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Operation	-5...35 °C
Ambient Air Temperature For Storage	-5...50 °C
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP4X
Environmental Characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	8.5 cm
Package 1 Length	12.6 cm
Package 1 Weight	90 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12.5 cm
Package 2 Width	17.5 cm
Package 2 Length	26 cm
Package 2 Weight	584 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	45
Package 3 Height	30 cm

Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	6.02 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations