

# Product data sheet

Specifications



2 Socket-outlet, New Unica, mechanism, 2P + E, 16A, Schuko, with shutter, painted, aluminium

NU306730AS

## Main

Range	New Unica
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism
Device Mounting	Flush
Socket Number	2
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Outlet Standard Description	Side earth
Ground Lug Position	45° ground lug
Rated Current	16 A

## Complementary

Device Application	Power supply
Cover Type	With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	4 modules
Fixing Mode	Clip-in
Colour Tint	Aluminium
Pilot Light	Red indicator lamp, colour: red, current consumption: 1.5 mA
Connections - Terminals	IPT (Isolates Piercing Terminal) Screw terminals
Cable Cross Section	0...2.5 mm² cable(s), 2 - cable stiffness: flexible 0...2.5 mm² cable(s), 2 - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	PC: mechanism cover
Surface Finish	Painted
Quantity Per Set	Set of 1 flow-pack

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60884-1 UNE 20315-1-1 UNE 20315-1-2 DIN VDE 0620-1
Product Certifications	EAC AENOR
Embedding Depth	31.1 mm
Depth	40.4 mm
Width	45 mm
Height	90 mm
Net Weight	0.079 kg
Surface Treatment	Painted
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

Ambient Air Temperature For Operation	-5...35 °C
Ambient Air Temperature For Storage	-5...50 °C
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D
Environmental Characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	4.5 cm
Package 1 Length	9.0 cm
Package 1 Weight	80.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.0 cm
Package 2 Width	22.0 cm
Package 2 Length	28.0 cm
Package 2 Weight	950.0 g
Unit Type Of Package 3	S04

Number Of Units In Package 3	90
Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	9.283 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Lower Impact Materials   Transparency   RoHS/REACH

## Resource performance

☒ Minimum Percentage Of Recycled Plastic Content   52

## Well-being performance

☒ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations