

Product data sheet

Specifications



2 Socket-outlet, New Unica, mechanism, 2P + E, 16A, French, with shutter, screwless terminals, IP3x, glossy, white

NU306918SE

Main

Range	New Unica
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism
Device Mounting	Flush
Socket Number	2
Outlet Poles Configuration	2P + E
Outlet Standard	French
Outlet Standard Description	Pin earth
Ground Lug Position	45° ground lug
Rated Current	16 A

Complementary

Device Application	Power supply
Cover Type	With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	4 modules
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003)
Pilot Light	Red indicator lamp, colour: red, current consumption: 1.5 mA
Connections - Terminals	Screwless terminals
Cable Cross Section	0...2.5 mm² cable(s), 2 - cable stiffness: flexible 0...2.5 mm² cable(s), 2 - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	PC: mechanism cover
Surface Finish	Glossy
Quantity Per Set	Set of 1 without packaging

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60884-1 NF C 61-314
Product Certifications	NF
Embedding Depth	30 mm
Depth	39.4 mm
Width	45 mm
Height	90 mm
Net Weight	0.077 kg
Surface Treatment	Untreated
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Operation	-5...35 °C
Ambient Air Temperature For Storage	-5...50 °C
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP3x
Environmental Characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	4.5 cm
Package 1 Length	9 cm
Package 1 Weight	73 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12.8 cm
Package 2 Width	12.3 cm
Package 2 Length	18.5 cm
Package 2 Weight	430 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	20

Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.035 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Lower Impact Materials

Resource performance

✓

Minimum Percentage Of Recycled Plastic Content

59

Eu Rohs Directive

Under investigation

Circularity Profile

No need of specific recycling operations