

# Product data sheet

Specifications



2 Socket-outlet, New Unica, mechanism, 2P + E, 16A, French, shutter, screwless terminals, IP3x, painted, anthracite

NU306954S

## Main

Range	New Unica
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism
Device Mounting	Flush
Socket Number	2
Outlet Poles Configuration	2P + E
Outlet Standard	French
Outlet Standard Description	Pin earth
Ground Lug Position	45° ground lug
Rated Current	16 A

## Complementary

Device Application	Power supply
Cover Type	With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	4 modules
Fixing Mode	Clip-in
Colour Tint	Anthracite (RAL 7021)
Pilot Light	Red indicator lamp, colour: red, current consumption: 1.5 mA
Connections - Terminals	Screwless terminals
Cable Cross Section	0...2.5 mm² cable(s), 2 - cable stiffness: flexible 0...2.5 mm² cable(s), 2 - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	PC: mechanism cover
Surface Finish	Painted
Quantity Per Set	Set of 1 without packaging

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60884-1 NF C 61-314
Product Certifications	NF
Embedding Depth	30 mm
Depth	39.4 mm
Width	45 mm
Height	90 mm
Net Weight	0.077 kg
Surface Treatment	Painted
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

Ambient Air Temperature For Operation	-5...35 °C
Ambient Air Temperature For Storage	-5...50 °C
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP3x
Environmental Characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	4.5 cm
Package 1 Length	9 cm
Package 1 Weight	72 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12 cm
Package 2 Width	12.5 cm
Package 2 Length	18.5 cm
Package 2 Weight	428 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	10

Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	1.06 kg

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Lower Impact Materials   Transparency

## Resource performance

✓ Minimum Percentage Of Recycled Plastic Content   60

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

Eu Rohs Directive   Compliant  
[EU RoHS Declaration](#)

China Rohs Regulation   [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure   [Product Environmental Profile](#)

Weee   The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile   No need of specific recycling operations