

# Product data sheet

Specifications



Push-button, New Unica, + NO push-button, 10A, 2 modules, screwless terminals, painted, IP4X, aluminium

NU320630L

! Discontinued

! Discontinued on: Jun 30, 2023

## Main

Range Of Product	New Unica
Product Or Component Type	Push-button
Device Presentation	Mechanism
Technology Type	Electromechanical
Switch Function	+ NO push-button
Number Of Rocker	1
Device Application	Light control
Colour Tint	Aluminium
Type Of Packing	Flow-pack

## Complementary

Rated Current	10 A
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Electrical Durability	20000 cycles, cos phi = 0.6
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening Distance	> 3 mm
Actuator	Rocker
Number Of Modules	2 modules
Connections - Terminals	Screwless terminals
Cable Cross Section	0...2.5 mm² rigid cable 0...2.5 mm² flexible cable
Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing CuZn37: terminals PBT (polybutylene terephthalate) GF30: release button
Marking	Light symbol
Surface Finish	Glossy
Specific Treatment - Integrated Within The Material	Painted

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fixing Mode	Clip-in
Width	45 mm
Height	45 mm
Depth	34.25 mm
Embedding Depth	21.15 mm
Net Weight	0.0231 kg
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-5...50 °C
Standards	LV directive IEC 60669-1
Product Certifications	CE AENOR EAC NF VDE
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

Ip Degree Of Protection	IP4X
Ik Degree Of Protection	IK04
Environmental Characteristic	Oil UV resistant Acetone Liquid soap Window-cleaning fluid Petrol Alcohol Bleach

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	24 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.2 cm
Package 2 Width	17.7 cm
Package 2 Length	18.5 cm
Package 2 Weight	314 g

Unit Type Of Package 3	S03
Number Of Units In Package 3	80
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.95 kg

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

Eu Rohs Directive	Under investigation
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations