

Product data sheet

Specifications



Socket-outlet, New Unica,
mechanism with fixing frame, 2P,
16A, European, with shutter, IP4X,
glossy, untreated, white

NU503318F

Main

Range	New Unica
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with zamak fixing frame
Device Mounting	Flush
Socket Number	1
Outlet Poles Configuration	2P
Outlet Standard	European
Rated Current	16 A
Condition Of Use	Indoor

Complementary

Device Application	Power supply
Cover Type	With shutter
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Number Of Modules	2 modules
Fixing Mode	Screws or claws
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals
Cable Cross Section	0...4 mm² cable(s), 2 - cable stiffness: flexible 0...4 mm² cable(s), 2 - cable stiffness: rigid
Minimum Load Breaking Capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical Durability	10000 cycles, cos phi = 0.8
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Material	PC: mechanism cover PC (polycarbonate) GF10 FR: casing CuZn37: terminals Zamak: fixing frame
Surface Finish	Glossy
Quantity Per Set	Set of 1 flow-pack

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60884-1 UNE 20315-1-1 UNE 20315-1-2 NF C 61-314
Product Certifications	EAC AENOR NF
Embedding Depth	27.5 mm
Depth	37 mm
Width	74.5 mm
Height	74.5 mm
Net Weight	0.0615 kg
Surface Treatment	Untreated
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Operation	-5...35 °C
Ambient Air Temperature For Storage	-5...50 °C
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP4X
Environmental Characteristic	Acetone Bleach UV resistant Petrol Oil Alcohol Window-cleaning fluid Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	7.1 cm
Package 1 Length	3.7 cm
Package 1 Weight	61.5 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations