

Product data sheet

Specifications



Exiway Power Control Multi - central battery system - 12 Main cct 240 lum (Max)

OVA18063

Main

Range	Exiway
Product Name	Exiway Power Control
Device Short Name	Exiway Power Control Multi
Product Or Component Type	Central battery system
Number Of Circuits	12
Number Of Light Blocks	240
Device Composition	6 main circuit module battery charger 17.5 A
Supply	Maintained Non-maintained

Complementary

[Us] Rated Supply Voltage	400 V 50 Hz
Poles Description	3P
Output Voltage	230 V AC 216 V DC
Display Type	LCD display
Communication Network Type	Ethernet TCP/IP
Communication Port Support	RS232 RS485
Communication Port Protocol	Modbus
Web Services	Web server
Language	Multi-language
Cover Type	Lockable cover to be ordered separately
Battery Type	Lead-acid battery to be ordered separately
Provided Equipment	I/O module internal Battery temperature sensor Centronics printer interface PS/2 keyboard external
Ambient Air Temperature For Operation	0...35 °C
Material	Sheet steel
Maximum Power	27000 W

Environment

Colour	Grey
--------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour Code	RAL 7035
Ip Degree Of Protection	IP20
Mounting Mode	Floor-standing
Electrical Insulation Class	Class I
Standards	IEC 60364-5-56 EN 55015 EN 50172 OVE/ONORM E 8002 EN 61547 DIN VDE 0100-718 EN 61000-3-3 EN 50171 DIN VDE 0108-100 EN 50272-2 EN 61000-3-2
Height	1800 mm
Width	600 mm
Depth	450 mm
Net Weight	100 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1