

Product data sheet

Specifications



Exiway Power Control Multi - central battery system - 24 Main cct 480 lum (Max)

OVA18067

Main

| | |
|---------------------------|--|
| Range | Exiway |
| Product Name | Exiway Power Control |
| Device Short Name | Exiway Power Control Multi |
| Product Or Component Type | Central battery system |
| Number Of Circuits | 24 |
| Number Of Light Blocks | 480 |
| Device Composition | 12 main circuit module battery charger 20 A |
| Supply | Non-maintained Maintained |

Complementary

| | |
|---------------------------------------|---|
| [Us] Rated Supply Voltage | 400 V 50 Hz |
| Poles Description | 3P |
| Output Voltage | 230 V AC 216 V DC |
| Display Type | LCD display |
| Communication Network Type | Ethernet TCP/IP |
| Communication Port Support | RS485 RS232 |
| Communication Port Protocol | Modbus |
| Web Services | Web server |
| Language | Multi-language |
| Cover Type | Lockable cover to be ordered separately |
| Battery Type | Lead-acid battery to be ordered separately |
| Provided Equipment | I/O module internal Battery temperature sensor Centronics printer interface PS/2 keyboard external |
| Ambient Air Temperature For Operation | 0...35 °C |
| Material | Sheet steel |
| Maximum Power | 27000 W |

Environment

| | |
|--------|------|
| Colour | Grey |
|--------|------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-----------------------------|--|
| Colour Code | RAL 7035 |
| Ip Degree Of Protection | IP20 |
| Mounting Mode | Floor-standing |
| Electrical Insulation Class | Class I |
| Standards | OVE/ONORM E 8002 EN 50171 DIN VDE 0100-718 EN 55015 EN 50272-2 DIN VDE 0108-100 EN 61000-3-3 EN 61000-3-2 EN 61547 IEC 60364-5-56 EN 50172 |
| Height | 1800 mm |
| Width | 600 mm |
| Depth | 450 mm |
| Net Weight | 100 kg |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation