

Product data sheet

Specifications



Exiway Power Control Multi - central battery system - 24 Main cct 480 lum (Max)

OVA18079

Main

Range	Exiway
Product Name	Exiway Power Control
Device Short Name	Exiway Power Control Multi
Product Or Component Type	Central battery system
Number Of Circuits	24
Number Of Light Blocks	480
Device Composition	6 main circuit module
Supply	Maintained Non-maintained

Complementary

[Us] Rated Supply Voltage	400 V 50 Hz
Poles Description	3P
Output Voltage	230 V AC 216 V DC
Display Type	LCD display
Communication Network Type	Ethernet TCP/IP
Communication Port Support	RS485
Communication Port Protocol	Modbus
Web Services	Web server
Language	Multi-language
Cover Type	Lockable cover to be ordered separately
Battery Type	Lead-acid battery to be ordered separately
Provided Equipment	I/O module internal
Ambient Air Temperature For Operation	0...35 °C
Material	Sheet steel

Environment

Colour	Grey
Colour Code	RAL 7035
Ip Degree Of Protection	IP21
Mounting Mode	Floor-standing

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Insulation Class	Class I
Standards	EN 61000-3-2 EN 50272-2 EN 55015 EN 61000-3-3 DIN VDE 0108-100 EN 50172 EN 61547 OVE/ONORM E 8002 IEC 60364-5-56 EN 50171 DIN VDE 0100-718
Height	550 mm
Width	600 mm
Depth	450 mm
Net Weight	20 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	60.0 cm
Package 1 Width	55.0 cm
Package 1 Length	45.0 cm
Package 1 Weight	45.0 kg