

Product data sheet

Specifications



Exiway Easyled- emergency light luminaire - std - non-maintained - 1 h - 300 lm

OVA38358

Main

Range	Exiway
Aesthetic name	Exiway Easyled
Product or component type	Emergency light fitting
Device application	Lighting
Function	Standard
Supply	Non-maintained
Number of batteries	1 x 4.8 V 1.6 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	LED integral LED 4 x 1 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

[Ue] rated operational voltage	220...230 V AC 50/60 Hz
Power consumption in VA	3.9 VA
Power consumption in W	1 W
Current consumption	16 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Luminous flux	Emergency condition: 300 lm
Type of glass	Serigraphed transparent glass
Material	Plastic: housing Plastic: cover
Device mounting	Flush wall Surface wall Surface ceiling Flush false ceiling
Height	37 mm
Width	292.5 mm

Depth	116.5 mm
Net weight	0.57 kg

Environment

IP degree of protection	IP42
IK degree of protection	IK07
Ambient air temperature for operation	5...30 °C
Fire resistance	850 °C
Product certifications	ENEC AENOR
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	619.0 g
Package 1 Height	4.7 cm
Package 1 width	12 cm
Package 1 Length	30 cm
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	7.915 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------