

# Product data sheet

Specifications



Circuit breaker basic frame,  
ComPact NSX160S, 100kA at  
415VAC 50/60 Hz, 160A, without  
trip unit, 4 poles

LV430396

! Discontinued

! Discontinued on: Dec 25, 2023

**Important message:** This product has been switched to new  
ComPacT range and is no longer commercialized.

## Main

Range	ComPact
Range Of Product	ComPact NSX100...250
Device Short Name	NSX160S
Product Or Component Type	Basic frame
Device Application	Distribution
Circuit Breaker Name	Compact NSX160S
Number Of Poles	4P
Neutral Position	Left
[In] Rated Current	160 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	100 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 120 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 15 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	S 100 kA 415 V AC
Control Type	Toggle
Mounting Mode	Fixed

## Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	100 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 120 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 15 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical Durability	40000 cycles conforming to IEC 60947-2
Electrical Durability	40000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 15000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 20000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 7500 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	Without protection
Width (W)	140 mm
Height (H)	161 mm
Depth (D)	86 mm

## Environment

Standards	EN/IEC 60947-2 UL 508
Product Certifications	CSA UL
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	14.5 cm
Package 1 Length	19.0 cm
Package 1 Weight	1.961 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	11
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	22.337 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>