

# Product data sheet

Specifications



## Exiway One - emergency light block - standard - non-maintained - 1 h - 380 lm

OVA38779

 **Discontinued on:** Feb 22, 2021

 **Discontinued**

### Main

Range	Exiway
Product Name	Exiway One
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Standard
Operational Mode	Non-maintained
Number Of Batteries	1 x 4.8 V 4 Ah Ni-Cd (Nickel-Cadmium)
Light Source	Fluorescent tube G5 8 W
Light Source Colour	White
Cover Type	Transparent
Wiring Device Additional Information	Can be inhibited with rest mode via Teleur range of remote controls

### Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	220...230 V AC/DC 50 Hz
Power Consumption In Va	8.4 VA
Power Consumption In W	1.6 W
Current Consumption	36 mA
Electrical Insulation Class	Class II
Autonomy	1 h
Charging Time	12 h
Type Of Glass	Fresnel glass
Device Mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Material	Housing: plastic Cover: plastic
Height	160 mm
Depth	68 mm
Width	375 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	AENOR ENEC
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.4 cm
Package 1 Width	8 cm
Package 1 Length	38.1 cm
Package 1 Weight	1.45 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>