

# Product data sheet

Specifications

## Exiway - false ceiling kit

OVA59823



### Main

Range	Exiway
Product Or Component Type	Flush mounting kit
Accessory / Separate Part Category	Mounting accessory
Colour	Grey

### Complementary

Range Compatibility	Exiway Exiway Smartled emergency light fitting
Product Compatibility	Exiway Smart Exiway Smartled
Kit Composition	1 false ceiling kit 2 screw diameter: 4 mm x 70 mm 2 washer 2 screw diameter: 4 mm x 55 mm
Material	Steel
Width	210 mm
Height	170 mm
Depth	42 mm
Cut-Out Dimensions	225 x 105 mm (Exiway Smart) 278 x 105 mm (Exiway Smartled)

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	17.2 cm
Package 1 Length	21.0 cm
Package 1 Weight	275.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	25
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.303 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>