

Product data sheet

Specifications



P850 digital I/O expander module - 8 digit I - 4(0,20mA) + 4(C) O - for ION8650

P850EB0

Main

Range Of Product	PowerLogic
Device Short Name	P850E
Product Or Component Type	I/O expansion module

Complementary

Product Compatibility	ION8650
Number Of Outputs	4 form C relay output 4 analog 0...20 mA
Number Of Inputs	8 digital
Provided Equipment	Without cable

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.800 cm
Package 1 Width	19.800 cm
Package 1 Length	59.500 cm
Package 1 Weight	1.140 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	3
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	4.070 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	12
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	28.280 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov