

Product data sheet

Specifications



Interlocked socket, Mureva PK,
panel mounting, 63A, 3P+N+E,
400V, IP65

PKB63T535

Main

Range	Mureva
Product Or Component Type	Interlocked socket
Device Short Name	Mureva socket
Plug, Socket Category	Low voltage
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Mounting Mode	Panel-mounted
[In] Rated Current	63 A
[Ue] Rated Operational Voltage	380...415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Protection Type	Without protection
Plug, Socket Material	Housing: self-extinguishing polymer
Contacts Material	Pins: stainless steel Screws: stainless steel
Connections - Terminals	Captive screws
Maximum Cable Cross Section	35 mm²
Maximum Cable Outer Diameter	25 mm
Net Weight	2.4 kg
Base Dimension	140 x 430 mm
Height	430 mm
Width	140 mm
Depth	116 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
-----------	----------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 62262
Fire Resistance	750 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.200 cm
Package 1 Width	19.400 cm
Package 1 Length	44.500 cm
Package 1 Weight	2.294 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	9
Package 2 Height	33.500 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	32.646 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Lower Impact Materials Transparency RoHS/REACH

Resource performance

 Minimum Percentage Of Recycled Plastic Content 50

Well-being performance

 Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations