

Product data sheet

Specifications



Decor - power socket-outlet -
mechanism - 20 A - 250 V - graphite
+ red

PRM04743

Main

Aesthetic Name	Decor
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism
Type Of Packing	Flow-pack

Complementary

[In] Rated Current	20 A
[Ue] Rated Operational Voltage	250 V AC
Material	ABS/PA
Number Of Modules	1
Embedding Depth	30.5 mm
Depth	39.4 mm
Length	43.4 mm
Height	39.4 mm
Width	23.5 mm
Connections - Terminals	Screw terminals
Cable Outer Diameter	3 mm
Cable Cross Section	4 mm ²
Awg Gauge	AWG 10
Fixing Mode	Clip-in

Environment

Standards	ABNT NBR 14.136 ABNT NBR NM 60.884
-----------	---------------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	9.5 cm
Package 1 Length	25.9 cm
Package 1 Weight	0.027 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations