

Product data sheet

Specifications



Resi9 Bronze door 3x18 Modules

R9H18423L

⚠ Discontinued on: May 16, 2022

⚠ Discontinued

Main

Range	Resi9
Product Or Component Type	Door
Accessory / Separate Part Category	Enclosure accessory
Range Compatibility	Resi9 enclosure

Complementary

Type Of Front Cover	Opaque
Number Of Horizontal Rows	3
9 Mm Pitches	36
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	54
Standards	IEC 61439-1 IEC 60670-1-24 IEC 61439-3
Fire Resistance	750 °C conforming to EN/IEC 60695-2-11
Ip Degree Of Protection	IP40 conforming to EN/IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262 IK08 conforming to EN 50102
Net Weight	850 g
Width	352.5 mm
Height	495.5 mm
Depth	27 mm
Colour Tint	Bronze

Environment

Ambient Air Temperature For Operation	-15...60 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	36.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	51 cm
Package 1 Weight	1.07 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information