

Product data sheet

Specifications



P116 dual power - In 5A - Ion 5A 0.1-40Ion - Vx 60-240VAC/ 60-250VDC

REL10276

⚠ Discontinued on: Dec 31, 2023

⚠ End-of-service on: Mar 31, 2024

⚠ Discontinued

Main

Range Of Product	MiCOM P11x
Device Short Name	P116
Relay Application	Feeder
Protection Type	ANSI 86 : lockout ANSI 49RMS : thermal overload protection ANSI 50N/51N : earth fault ANSI 50BF : breaker failure ANSI 50/51 : phase overcurrent ANSI 46 : negative sequence/unbalance
Communication Port Protocol	Modbus RTU IEC 60870-5-103

Complementary

Type Of Measurement	Current
Auxiliary Supply	60...240 V AC 60...250 V DC
[Us] Rated Supply Voltage	90...240 V AC 71...265 V 60...250 V DC 48...300 V
Control And Monitoring Type	Latching/acknowledgement Switching of groups of settings
Metering Type	Phase currents
Network And Machine Diagnosis Type	Fault recording Event recording
Display Type	LCD display: 2 lines of 16 characters ASCII (European characters) and 9 key
Earth Current Inputs	5 A
Communication Port Support	USB RS485

Environment

Device Mounting	Flush
Mounting Mode	Flush-mounted

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	15.8 cm
Package 1 Length	25.6 cm
Package 1 Weight	2.75 kg