

# Product data sheet

Specifications



## Circuit breaker, ComPact NSX630N, 50kA/415VAC, MicroLogic 2.3 trip unit 630A, 4 poles 4d

LV432894

**!** To be discontinued on: 31 March 2023

**!** To be discontinued

**Important message :** This product has been switched to new ComPact range and is no longer commercialized. It will continue to be available in H1 2023 only limited to specific projects.

### Main

Range	ComPact
Product name	ComPact NSX
Range of product	ComPact NSX400...630
Device short name	NSX630N
Product or component type	Circuit breaker
Device application	Distribution
Number of poles	4P
Protected poles description	4t 3t 3t + N/2
Neutral position	Left
[In] rated current	630 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	85 kA at 240 V AC 50/60 Hz conforming to UL 508 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 20 kA at 600 V AC 50/60 Hz conforming to UL 508 50 kA at 480 V AC 50/60 Hz conforming to UL 508 50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 42 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	N 50 kA 415 V AC
Trip unit name	Micrologic 2.3
Trip unit technology	Electronic
Trip unit protection functions	LSol
Control type	Toggle
Circuit breaker mounting mode	Fixed

## Complementary

<b>[Ui] rated insulation voltage</b>	800 V AC 50/60 Hz
<b>[Uimp] rated impulse withstand voltage</b>	8 kV
<b>[Ics] rated service short-circuit breaking capacity</b>	11 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 10 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 30 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 42 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
<b>Mechanical durability</b>	15000 cycles
<b>Electrical durability</b>	2000 cycles at 690 V In 6000 cycles at 690 V In/2 4000 cycles at 440 V In 8000 cycles at 440 V In/2
<b>Mounting support</b>	Backplate
<b>Upside connection</b>	Front
<b>Downside connection</b>	Front
<b>Connection pitch</b>	45 mm
<b>Protection type</b>	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
<b>Trip unit rating</b>	630 A at 40 °C
<b>Long-time pick-up adjustment type Ir (thermal protection)</b>	Adjustable 9 settings
<b>[Ir] long-time protection pick-up adjustment range</b>	250...630 A
<b>Long-time protection delay adjustment type tr</b>	Fixed
<b>[Tr] long-time protection delay adjustment range</b>	16 s at 6 x Ir
<b>Thermal memory</b>	20 minutes before and after tripping
<b>Short-time protection pick-up adjustment type Isd</b>	Adjustable 9 settings
<b>[Isd] Short-time protection pick-up adjustment range</b>	1.5...10 x Ir
<b>Short-time protection delay adjustment type tsd</b>	Fixed
<b>Instantaneous protection pick-up adjustment type Ii</b>	Fixed
<b>[Ii] instantaneous protection pick-up adjustment range</b>	6900 A
<b>Earth-leakage protection</b>	Without
<b>Neutral protection settings</b>	0.5 x Ir (3t + N/2) 1 x Ir (4t) No protection (3t)
<b>Zone selective interlocking ZSI</b>	Without
<b>Number of slots for electrical auxiliaries</b>	6 slot(s)
<b>Local signalling</b>	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload
<b>Width (W)</b>	185 mm
<b>Height (H)</b>	255 mm
<b>Depth (D)</b>	110 mm

Net weight	8.13 kg
------------	---------

## Environment

Standards	EN/IEC 60947
Product certifications	CCC EAC Marine
Overvoltage category	Class II
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m without derating 2000 m...5000 m with derating

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.7 cm
Package 1 Width	20.0 cm
Package 1 Length	28.9 cm
Package 1 Weight	7.43 kg
Unit Type of Package 2	S04
Number of Units in Package 2	3
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	23.158 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

---

Warranty

18 months

## Recommended replacement(s)

LV432894 is replaced by:

---

1x



Circuit breaker, ComPacT NSX630N, 50kA/415VAC, 4 poles, MicroLogic 2.3 trip unit  
630A  
C63N42D630

---