

Product data sheet

Specifications



PowerLogic P5F30 48-250V 3CT 2Io 4VT 16DI-12DO RSTP Eth RJ45

REL50453

Main

| | |
|--|---|
| Range Of Product | PowerLogic P5 |
| Product Or Component Type | Protection and control relay |
| Relay Application | Feeder - directional over current |
| Product Reference | P5F30-BACB-GABAH-AAEA |
| Mounting Case Size | 30TE |
| Device Mounting | Flush |
| Mounting Mode | Withdrawable |
| Power Supply | 48...250 V DC 100...230 V AC |
| Measuring Inputs | : 1/5 A CT phase current 3 : 1/5 A CT residual current 1 : 1 A CT residual current 1 : VT voltage 4 |
| Number Of Sensors | 0 temperature sensor(s) 0 arc sensor(s) |
| Number Of Digital Inputs (Di) | 16 |
| Number Of Digital Outputs (Do) | 11 DO 1 watchdog |
| Number Of Analogue Inputs | 0 |
| Number Of Analogue Outputs | 0 |
| Communication Ports | RJ45 2 rear Extension port 1 rear with backup memory USB port 2 front |
| Communication Protocols | IEC 61850 ed. 1 IEC 61850 ed. 2 DNP3 over ethernet Modbus TCP EtherNet/IP |
| Redundancy Communication Port Protocol | RSTP |
| Cybersecurity | Port hardening Firmware signature Client IP address filter Secured communication with associated tools Security policy management Role-based access control Security log LDAP RADIUS based user authentication IEC 62442-4-2 SL1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------|---|
| Protection Functions | Phase overcurrent 50/51 Directional phase overcurrent 67 Earth fault overcurrent 50N/51N Restricted earth fault 64REF Directional earth fault 67N Transient earth fault 67NI Neutral admittance 21YN Earth fault wattmetric 32N Capacitor bank unbalance 51C Broken conductor 46 I2/I1 Current unbalance 46 I2/I1 Cold load pick-up Switch ON to fault (SOTF) H2 detection H5 detection Breaker failure 50BF Directional active underpower 37P Fault locator 21FL Recloser 79 Negative sequence overcurrent 46 Overvoltage 59 Undervoltage 27 Earth fault overvoltage 59N Underfrequency 81/81N Rate of change of frequency 81R Synchro-check 25 Lockout relay 86 CT supervision 60 VT supervision 60 Programmable stages 99 Programmable logic Programmable curve |
| Measurement Functions | Current 3-phase Current zero sequence Current positive sequence Current negative sequence Current ratio of negative and positive Phasor diagram of currents or voltages Current 2nd, 15th harmonics with THD Voltage 3-phase Voltage residual Voltage zero sequence Voltage positive sequence Voltage negative sequence Frequency |
| Control Functions | Switchgear control and monitoring Programmable switchgear interlocking Local/remote control |
| Controllable Switchgear Devices | 6 controlled + 2 monitored objects |
| Number Of Setting Groups | 4 |
| Monitoring Functions | Trip circuit supervision 74 Circuit breaker monitoring Relay self-monitoring |
| Logs And Records | Event recording Disturbance recording Tripping context Relay maintenance |
| Switchgear Diagnosis Type | CT/VT supervision ANSI code: 60 Trip circuit supervision ANSI code: 74 |
| Connections - Terminals | Screw (digital input/output) Ring lugs (analog inputs and outputs) |

Complementary

| | |
|-------------------------------|---|
| Time Synchronisation Protocol | SNTP |
| Software Name | EcoStruxure Power Device ESetup Easergy Pro: virtual simulation test |
| Web Server | Embedded HTTP server |

| | |
|------------------|---|
| Display Type | Colour LCD 480 x 272 pixels |
| Number Of Key | 7 customizable |
| Local Signalling | 4 x LED 10 x LED tri-colour programmable |
| Height | 176 mm |
| Width | 152 mm |
| Depth | 219 mm |
| Net Weight | 3.5 kg |

Environment

| | |
|---------------------------------------|--|
| Electromagnetic Compatibility | Emission tests class A conforming to CISPR 11 Emission tests class A conforming to CISPR 32 Emission tests conforming to IACS E10 EMC immunity class 4 conforming to IEC 61000-4-2 EMC immunity class 4 conforming to ANSI C37.90.3 EMC immunity level 3 conforming to IEC 61000-4-3 EMC immunity conforming to ANSI C37.90.2 EMC immunity conforming to GOST 32137 EMC immunity conforming to GOST 30804.4.3 EMC immunity conforming to IACS E10 EMC immunity level 5 conforming to IEC 61000-4-8 EMC immunity level 5 conforming to IEC 61000-4-9 EMC immunity level 5 conforming to IEC 61000-4-10 EMC immunity level 3 conforming to IEC 61000-4-6 EMC immunity level 3 conforming to IEC 61000-4-18 EMC immunity conforming to ANSI C37.90.1 EMC immunity conforming to IEC 61000-4-12 EMC immunity conforming to GOST 30804.4.12 EMC immunity level 4 conforming to IEC 61000-4-16 EMC immunity level 4 conforming to IEC 61000-4-4 EMC immunity level 4 conforming to IEC 61000-4-5 |
| Mechanical Robustness | Vibrations (level: class 2) conforming to IEC 60255-21-1 Vibrations conforming to GOST 17516.1 Vibrations conforming to IACS E10 Shocks (level: class 2) conforming to IEC 60255-21-2 Earthquakes (level: class 2) conforming to IEC 60255-21-3 |
| Climatic Withstand | Exposure to cold conforming to IEC 60068-2-1 Exposure to dry heat conforming to IEC 60068-2-2 Exposure to damp heat in service conforming to IEC 60068-2-78 Exposure to damp heat in service conforming to IEC 60068-2-30 Temperature variation conforming to IEC 60068-2-14 Salt mist conforming to IEC 60068-2-52 Influence of corrosion/gas test 2 conforming to IEC 60068-2-60 Influence of corrosion/gas test 4 conforming to IEC 60068-2-60 Influence of corrosion/gas test 2 conforming to IEC 60721-3-3 Influence of corrosion/gas test 4 conforming to IEC 60721-3-3 |
| Ambient Air Temperature For Operation | -40...85 °C (16 h) -40...70 °C (96 h) |
| Ambient Air Temperature For Storage | -40...85 °C |
| Ip Degree Of Protection | IP54 conforming to IEC 60529 |
| Relative Humidity | 0...93 % at 40 °C, without condensation, 56 days 93...95 % at 25...55 °C, 6 cycles, 12 + 12 hours |
| Maximum Operating Altitude | 2000 m |
| Protective Treatment | Conformal coating conforming to IEC 60068-2-52:Kb/1 Conformal coating conforming to IEC 60068-2-60:Ke Conformal coating conforming to IEC 60721-3-3:3C2 |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

| | |
|------------------|---------|
| Package 1 Height | 30.0 cm |
| Package 1 Width | 30.0 cm |
| Package 1 Length | 35.0 cm |
| Package 1 Weight | 4.5 kg |

Contractual warranty

| | |
|----------|--|
| Warranty | Up to 10 years extended warranty (Standard warranty 2 years. Please check with your local SE representative for extended warranty availability and conditions) |
|----------|--|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Rohs Exemption Information

Yes

Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |