

Product data sheet

Specifications



Circuit breaker, ComPact NSX250HB2, 100kA/690VAC, TMD trip unit 250A, 4 poles 4d

LV433493

⚠ Discontinued on: Oct 26, 2023

⚠ Discontinued

Important message: This product has been switched to new ComPacT range and is no longer commercialized.

Main

| | |
|--|---|
| Range | ComPact |
| Product Name | ComPact NSX |
| Range Of Product | ComPact NSX100...250 |
| Device Short Name | NSX250HB2 |
| Product Or Component Type | Circuit breaker |
| Device Application | Distribution |
| Number Of Poles | 4P |
| Protected Poles Description | 4t |
| Neutral Position | Left |
| [In] Rated Current | 250 A at 40 °C |
| [Ue] Rated Operational Voltage | 690 V AC 50/60 Hz |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Suitability For Isolation | Yes conforming to EN/IEC 60947-2 |
| Utilisation Category | Category A |
| [Icu] Rated Ultimate Short-Circuit Breaking Capacity | 100 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance Level | HB2 100 kA 690 V AC |
| Trip Unit Name | TM-D |
| Trip Unit Technology | Thermal-magnetic |
| Trip Unit Protection Functions | LI |
| Control Type | Toggle |
| Circuit Breaker Mounting Mode | Fixed |

Complementary

| | |
|---|---|
| [Ui] Rated Insulation Voltage | 800 V AC 50/60 Hz |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV |
| [Ics] Rated Service Short-Circuit Breaking Capacity | 100 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 100 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---|---|
| Mechanical Durability | 20000 cycles |
| Electrical Durability | 5000 cycles at 690 V In 10000 cycles at 690 V In/2 10000 cycles at 440 V In 20000 cycles at 440 V In/2 |
| Mounting Support | Backplate |
| Upside Connection | Front |
| Downside Connection | Front |
| Connection Pitch | 35 mm |
| Protection Type | L : for overload protection (thermal) I : for short-circuit protection (magnetic) |
| Trip Unit Rating | 250 A at 40 °C |
| Long-Time Pick-Up Adjustment Type Ir (Thermal Protection) | Adjustable |
| [Ir] Long-Time Protection Pick-Up Adjustment Range | 0.7...1 x In |
| Long-Time Protection Delay Adjustment Type Tr | Fixed |
| [Tr] Long-Time Protection Delay Adjustment Range | 120...400 s at 1.5 x In 15 s at 6 x Ir |
| Short-Time Protection Pick-Up Adjustment Type Isd | Adjustable |
| [Isd] Short-Time Protection Pick-Up Adjustment Range | 5...10 x In |
| Short-Time Protection Delay Adjustment Type Tsd | Fixed |
| Earth-Leakage Protection | Without |
| Neutral Protection Settings | 1 x Ir (4t) |
| Number Of Slots For Electrical Auxiliaries | 5 slot(s) |
| Width (W) | 140 mm |
| Height (H) | 161 mm |
| Depth (D) | 86 mm |
| Net Weight | 2.8 kg |

Environment

| | |
|---------------------------------------|--|
| Standards | EN/IEC 60947 |
| Product Certifications | CCC EAC Marine |
| Overvoltage Category | Class II |
| Electrical Shock Protection Class | Class II |
| Pollution Degree | 3 conforming to IEC 60664-1 |
| Ip Degree Of Protection | IP40 conforming to IEC 60529 |
| Ik Degree Of Protection | IK07 conforming to IEC 62262 |
| Ambient Air Temperature For Operation | -25...70 °C |
| Ambient Air Temperature For Storage | -50...85 °C |
| Relative Humidity | 0...95 % |
| Operating Altitude | 0...2000 m without derating 2000 m...5000 m with derating |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 13.5 cm |
| Package 1 Width | 14.1 cm |
| Package 1 Length | 19.2 cm |
| Package 1 Weight | 2.723 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|---------------------------|--|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |