

# Product data sheet

Specifications



interface plug in relay, Harmony  
Electromechanical Relays, 10A,  
1CO, with LED, lockable test but to  
n, 12V DC

RXG12JD

## Main

|  |                                  |
|--|----------------------------------|
| Range Of Product                             | Harmony Electromechanical Relays |
| Series Name                                  | Interface relay                  |
| Product Or Component Type                    | Plug-in relay                    |
| Device Short Name                            | RXG                              |
| Contacts Type And Composition                | 1 C/O                            |
| [lthe] Conventional Enclosed Thermal Current | 10 A at -40...55 °C              |
| Local Signalling                             | Flag                             |

## Complementary

|                                |  |
|--------------------------------|--|
| Status Led                     | With   |
| [le] Rated Operational Current | 10 A at 30 V (DC) conforming to UL<br>10 A at 30 V (DC) conforming to IEC<br>10 A at 250 V (AC) conforming to IEC<br>10 A at 250 V (AC) conforming to UL |
| Electrical Durability          | 100000 cycles for NO resistive load at 55 °C<br>100000 cycles for NC resistive load at 55 °C   |
| Coil Resistance                | 270 Ohm +/- 10 %   |
| Shock Resistance               | 20 gn in operation<br>100 gn not in operation  |
| Mounting Position              | Any position   |
| [Uc] Control Circuit Voltage   | 12 V DC  |
| Colour Of Cover                | Standard   |
| Drop-Out Voltage Threshold     | >= 0.1 Uc DC   |
| Load Current                   | 10 A at 250 V AC   |
| Minimum Switching Capacity     | 500 mW at 100 mA, 5 V DC   |
| Maximum Switching Capacity     | 2500 VA  |
| Control Type                   | Lockable test button   |
| Torque Value                   | 0.8 N.m  |
| Contact Resistance             | 100 mOhm   |
| Insulation Resistance          | 1000 MOhm at 500 V DC  |
| Electrical Insulation Class    | Class F  |
| Mechanical Durability          | 10000000 cycles  |
| Safety Reliability Data        | B10d = 100000  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                               |  |
|-------------------------------|--|
| Operating Time                | 20 ms  |
| Reset Time                    | 20 ms  |
| Overvoltage Category          | III  |
| Maximum Switching Voltage     | 250 V AC<br>30 V DC  |
| Protection Category           | RT I   |
| Operating Rate                | <= 1800 cycles/hour under load<br><= 18000 cycles/hour no-load   |
| Pollution Degree              | 2  |
| Utilisation Coefficient       | 20 %   |
| [UI] Rated Insulation Voltage | 250 V conforming to IEC<br>300 V conforming to CSA<br>300 V conforming to UL   |
| Dielectric Strength           | 1000 V AC between contacts with micro disconnection<br>5000 V AC between coil and contact with reinforced insulation |
| Test Levels                   | Level A group mounting   |
| Device Presentation           | Complete product   |
| Contacts Material             | Silver alloy (AgSnO2In2O3)   |
| Net Weight                    | 0.02 kg  |

## Environment

|                                       |  |
|---------------------------------------|--|
| Standards                             | UL 508<br>CSA C22.2 No 14<br>IEC 61810-1   |
| Product Certifications                | CSA<br>CE<br>EAC<br>UL<br>DNV-GL   |
| Ambient Air Temperature For Storage   | -40...85 °C  |
| Ambient Air Temperature For Operation | -40...70 °C  |
| Ip Degree Of Protection               | IP40   |
| Relative Humidity                     | 10...85 %  |
| Vibration Resistance                  | 3 gn, amplitude = +/- 0.75 mm (f = 10...150 Hz)in operation<br>5 gn, amplitude = +/- 0.75 mm (f = 10...150 Hz)not in operation |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 3.556 cm |
| Package 1 Width              | 3.302 cm |
| Package 1 Length             | 1.27 cm  |
| Package 1 Weight             | 22.68 g  |

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free


✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                           |  |
|---------------------------|--|
| Reach Regulation          | <a href="#">REACH Declaration</a>  |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>   |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile       | No need of specific recycling operations   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Dimensions Drawings


Dimensions



Connections and Schema

Wiring Diagram


---



Performance Curves

Performance Curves

Maximum Switching Capacity



X : Switching voltage (V)

Y : Switching current (A)

(1) AC Resistive Load


(2) AC Inductive Load  $\cos(\phi)=0.4$

(3) DC Resistive Load

(4) DC Inductive Load ( $L/R=7\text{ms}$ )

Life Expectancy

Resistive Load




X : Contact Current (A)

Y : Operating Cycle Number

Life Expectancy

Inductive Load




X : Contact Current (A)  
Y : Operating Cycle Number

**NOTE:** These are typical curves, actual durability depends on load, environment, duty cycle, etc.

Coil Operating Range

DC Coil Operating Range VS Ambient Temperature



X : Ambient temperature (°C)

Y : Coil voltage (U/Uc)

(1) Permitted operating range area