

Product data sheet

Specifications



Miluz - USB charger 2.0 2.1A + US socket outlet 2P+E 15A 250V - assembled - whit

S3B19810

⚠ Discontinued on: Jun 7, 2023

⚠ Discontinued

Main

Range	Miluz
Aesthetic Name	Bossa
Product Or Component Type	USB charger + socket-outlet
Fixing Mode	By screws

Complementary

Outlet Standard	American
Outlet Standard Description	With earthing contact
Ground Lug Position	Straight 0° position
Integrated Connection Type	2 socket-outlet 250 V AC 15 A 50/60 Hz 2 USB port 5 V DC 2.1 A
Power Consumption In W	0.1 W
Input Power	7.5 W
Device Mounting	Flush
Device Presentation	Complete mechanism
Mounting Support	Mounting box (3 modules)
Outlet Poles Configuration	2P + E with shutter
Number Of Modules	3 modules
Surface Finish	Glossy
Surface Treatment	Untreated
Type Of Packing	Blister
Quantity Per Set	Set of 6
Sale Per Indivisible Quantity	1
Ambient Air Temperature For Storage	-5...50 °C
Protection Type	Short time short-circuit protection
Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	15...95 %
Service Life In Cycles	5000 cycles
Connections - Terminals	Screw terminal
Number Of Terminals	2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Screwdriver Shape	Phillips combined
Number Of Cables	2
Clamping Connection Capacity	1.5...2.5 mm² for flexible cable(s) 1.5...2.5 mm² for rigid cable(s)
Material	Thermoplastic ABS-UV stabilised: centre plate PC (polycarbonate) GF10 FR: casing
Wire Stripping Length	4 mm
Product Compatibility	LGE Samsung Sony Ericsonn Nokia Apple Huawei Technologies Atmel Qualcomm Motorola Mobility Texas Instruments TCT mobile (ALCATEL) Research in Motion Emblaze mobile
Height	115 mm
Width	52 mm
Depth	77 mm
Net Weight	0.1 kg

Environment

Standards	NEMA 5-15R EN 62684 ETSI EN 300 489-34 EN 60950-1
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive 2009/125/EC - ecodesign
Electrical Insulation Class	Class II
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP41
Environmental Characteristic	Petrol Bleach Acetone Alcohol Window-cleaning fluid Hydrogen peroxide (H2O2) Liquid soap Oil UV resistant

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	5.2 cm
Package 1 Length	7.7 cm
Package 1 Weight	100 g
Unit Type Of Package 2	BB1

Number Of Units In Package 2	6
Package 2 Height	15.8 cm
Package 2 Width	21.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	600 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations