

Product data sheet

Specifications



Orion - assembled duplex American socket outlet 2P+E isolated 20A 250V hospital

S713340N45

⚠ Discontinued on: Dec 15, 2022

⚠ Discontinued

Main

Range Of Product	Orion
Range	Orion
Product Or Component Type	Socket-outlet
Device Presentation	Complete product
Outlet Poles Configuration	2P + E without shutter
Fixing Mode	By screws
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Sale Per Indivisible Quantity	1
Rated Current	20 A at 125 V AC 50/60 Hz

Complementary

Number Of Power Socket Outlets	2
Device Mounting	Flush
Outlet Standard Description	Isolated earth Hospital grade
Outlet Standard	American
Ground Lug Position	Straight 0° position
Number Of Modules	3 modules 120 x 82.5 mm
Surface Finish	Glossy
Surface Treatment	Untreated
Ambient Air Temperature For Storage	-20...60 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	-5...35 °C
Electrical Durability	5000 cycles
Connections - Terminals	3 screw terminals
Screwdriver Shape	Philips
Number Of Cables	2
Clamping Connection Capacity	1.5...4 mm² for rigid cable(s) 1.5...4 mm² for stranded cable(s) 1.5...4 mm² for flexible cable(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Wire Stripping Length	18 mm
Material	PA (polyamide): casing PA (polyamide): centre plate ABS (acrylonitrile butadiene-styrene): adaptor frame Thermoplastic ABS-UV stabilised: cover frame
Height	120 mm
Width	82.5 mm
Depth	38.2 mm
Embedding Depth	28.5 mm
Net Weight	0.138 kg
Standards	UL 498 UL 94

Environment

Product Certifications	NOM
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20
Environmental Characteristic	Acetone Oil UV resistant Window-cleaning fluid Petrol Alcohol Liquid soap Bleach Hydrogen peroxide (H2O2)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	9.3 cm
Package 1 Length	20.0 cm
Package 1 Weight	136.0 g