

# Product data sheet

Specifications



## Séquence5 - dolly switch - 2-way - 10 AX - Nickel

S800204NB

⚠ Discontinued on: Sep 30, 2021

⚠ Discontinued

### Main

|                               |                                |
|-------------------------------|--------------------------------|
| Range Of Product              | Sequence5                      |
| Product Or Component Type     | Switch                         |
| Device Presentation           | Complete product               |
| Switch Additional Information | With internal power connection |
| Switch Application            | On/off switching               |
| Type Of Packing               | Box                            |
| Quantity Per Set              | Set of 1                       |
| Sale Per Indivisible Quantity | 1                              |

### Complementary

|                                |  |
|--------------------------------|--|
| Device Mounting                | Flush  |
| Switch Function                | 2-way  |
| Number Of Rocker               | 1  |
| Actuator                       | Small dolly rocker   |
| Fixing Mode                    | By screws  |
| Colour Tint                    | Nickel   |
| Surface Finish                 | Glossy   |
| Rated Current                  | 10 AX at 250 V AC 50 Hz  |
| Minimum Load Breaking Capacity | 200 operations 1.25 In and 1.1 Un with cos φ = 0.3   |
| Service Life In Cycles         | 20000 cycles at ON and OFF at rated voltage with cos φ = 0.6   |
| Electrical Durability          | 20000 cycles at ON and OFF at rated voltage with cos φ = 0.6   |
| Number Of Terminals            | 3 screwless terminals  |
| Shape Of Screw Head            | Pozidriv No 1  |
| Clamping Connection Capacity   | 1 x 1.5...2 x 2.5 mm² for rigid cable(s)<br>1 x 1.5...2 x 2.5 mm² for flexible cable(s)<br>1 x 1.5...2 x 2.5 mm² for stranded cable(s) |
| Wire Stripping Length          | 12 mm  |
| Material                       | Metal  |
| Height                         | 80 mm  |
| Width                          | 80 mm  |
| Depth                          | 49 mm  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                 |          |
|-----------------|----------|
| Embedding Depth | 35 mm    |
| Net Weight      | 0.235 kg |

## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient Air Temperature For Storage   | -5...50 °C  |
| Dielectric Strength                   | 2000 V  |
| Ambient Air Temperature For Operation | 5...35 °C   |
| Standards                             | EN 60669-1<br>2006/95/EEC   |
| Product Certifications                | LCIE: CCA-FR_598285B<br>LCIE: NF 604950<br>NF   |
| Ik Degree Of Protection               | IK04  |
| Ip Degree Of Protection               | IP21D   |
| Environmental Characteristic          | Window-cleaning fluid<br>Oil<br>UV resistant<br>Bleach<br>Alcohol<br>Acetone<br>Petrol<br>Liquid soap |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 5 cm    |
| Package 1 Width              | 10 cm   |
| Package 1 Length             | 12.5 cm |
| Package 1 Weight             | 270 g   |

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation

---