

# Product data sheet

Specifications



## Roof Top Controller: Echelon, 2H/2C

SE7600B5045E

 **Discontinued on:** Dec 31, 2021

 **Discontinued**

### Main

Product Name	SE7000 Series
Device Short Name	SE7600B
Product Or Component Type	Room controller
Device Application	Low voltage rooftop Staging equipment (RTU/HP)
Net Weight	0.34 kg
Awg Gauge	AWG 22...AWG 18
Height	124.97 mm
Product Specific Application	2-stage heating 2-stage cooling
Width	86.87 mm
Directives	89/336/EEC - electromagnetic compatibility
Depth	29.97 mm
Ambient Air Temperature For Operation	-0...50 °C
Market Segment	Residential
Ambient Air Temperature For Storage	-30...50 °C
Measurement Accuracy	Temperature: +/- 0.9 °F, (at 70 °F typically calibrated)
Product Certifications	FCC conforming to CFR 47 part 15 class A CE C-Tick conforming to AS/NZS CISPR 22 UL listed file E27734 CCN XPAX UL listed file E27734 CCN XPAX7
Information Displayed	Temperature: - 40...122 °F
Network Frequency	60 Hz 50 Hz
Communication Port Protocol	LonWorks
Temperature Setting Range	4...32 °C heating -17 °C per step 12...38 °C cooling
Sensor Type	10 kOhm T2 NTC thermistor temperature
[Us] Rated Supply Voltage	10...30 V AC 50/60 Hz
Input Type	2 x dry contact
Output Current	1 A digital output (maximum) 3 A digital output (inrush) <= 5 mA analog output

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output Type	2 xuniversal
Output Voltage	30 V AC for digital output 0...10 V DC for analog output
Standards	FCC part 15 Subpart B UL 873 CSA C22.2 No 24 ICES-003
Relative Humidity	0...95 % RH, non-condensing
Storage Relative Humidity	0...95 % RH, non-condensing
Range	EcoStruxure Building Expert
Economizer	No
Humidity Control	No
Pir Cover	No
Scheduling	No

## Complementary

Device Presentation	Without cover
Rated Operational Power In Va	2 VA
Internal Resistance	>= 2 kOhm
Connections - Terminals	Screw terminal
Contact Operation	5 standard push-button
Regulation Loop	For heating: adjustable P regulator by -17 °C (factory setting) For cooling: adjustable P regulator by -17 °C (factory setting)
Range Compatibility	EcoStruxure Building Expert communication card EcoStruxure Building Expert sensor EcoStruxure Building Expert temperature sensor EcoStruxure Building Expert relay EcoStruxure Building Expert sensor coverplate

## Environment

Electrical Insulation Class	Class II
-----------------------------	----------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	15.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	500.0 g

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: Cancer and Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

---