

Product data sheet

Specifications



APC Smart-UPS C, Line Interactive, 1000VA, Tower, 230V, 8x IEC C13 outlets, USB and Serial communication, AVR, Graphic LCD

SMC1000I

⚠ To be discontinued

⚠ To be discontinued on: Sep 25, 2024

⚠ To be end-of-service on: Feb 28, 2026

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead Time	Usually in Stock


Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Rated Power In W	600 W
Rated Power In Va	1000 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 320 C14
Output Connection Type	8 IEC 320 C13 2 IEC Jumpers
Battery Type	Lead-acid battery
Provided Equipment	CD with software Documentation CD USB cable

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Voltage	24 V
Extended Runtime	0
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Life	3...5 year(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Replacement Battery	APCRBC142 
Battery Charger Power	56 W rated

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Product Web Sub-Family	Entry level
Redundant	No

Physical

Colour	Black
Height	21.9 cm
Width	17.1 cm
Depth	43.9 cm
Net Weight	17.27 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	Yes

Input

Input Voltage Limits	170...300 V adjustable 180...287 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic Distortion	Less than 5 % at full load
Maximum Configurable Power In Va	1000 VA
Maximum Configurable Power In W	600 W
Ups Type	Line interactive
Wave Type	Sine wave
Output Frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE CSA GOST VDE EAC
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic Level	41 dBA
Heat Dissipation	100 Btu/h
Operating Altitude	0...10000 ft
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-15...45 °C
Storage Altitude	0.00...15240.00 m
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control Panel	Multifunction LCD status and control console
Free Slots	0
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge Energy Rate	455 J
Noise Suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	37.6 cm
Package 1 Width	59.5 cm
Package 1 Length	32.8 cm
Package 1 Weight	19.55 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information