


Product data sheet

Specifications



Anti Harmonic PowerLogic PFC detuned reactor, 50kvar 252Hz (4.2) 5.7% 60Hz 480V

LVR05500B48T

Main

Range	PowerLogic
Device short name	DR
Product or component type	Detuned reactor
Network frequency	60 Hz
Reactive power rating	50 kvar for 480 V AC 60 Hz
Network rated voltage	480 V AC 60 Hz
Tuning order	4.2 - 252 Hz - 5.7 % - 60 Hz

Complementary

Power losses (max)	320 W
Value of inductance	0.71 mH
Inductance tolerance	- 5 % to 5 % per phase
Fundamental current rating	60.1 A
RMS current rating	73.4 A
Electrical insulation class	Class H
[Ui] rated insulation voltage	1.1 kV
Dielectric test voltage	4 kV 60 Hz 1 minute
[Imp] maximum permanent current	1.3 x I1
Harmonic current spectrum	2.9 % x I3 67.8 % x I5 18.6 % x I7 6.2 % x I11
Dynamic withstand current	2.2 x Isc
[Ith] conventional free air thermal current	2 A at 250 V AC 50 Hz
Type of installation	Indoor installation
Type of cooling	Forced convection
Connections - terminals	Pad terminal
Fixing center	200 x 125 mm
Height	270 mm
Width	260 mm

Depth	200 mm
Net weight	24.5 kg

Environment

Standards	IEC 60068
IP degree of protection	IP00
Operating altitude	<= 2000 m
Ambient air temperature for operation	0...55 °C at <= 1000 m 0...50 °C at > 1000...2000 m
Average ambient air temperature for operation	50 °C at <= 1000 m (average over 24 hours) 40 °C at <= 1000 m (average over 1 year) 45 °C at > 1000...2000 m (average over 24 hours) 35 °C at > 1000...2000 m (average over 1 year)
Climatic withstand	Relative humidity: 20...80 % Salt mist (400 V/50 Hz) : 250 hours

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	31.000 cm
Package 1 Width	35.000 cm
Package 1 Length	55.000 cm
Package 1 Weight	29.000 kg
Unit Type of Package 2	P06
Number of Units in Package 2	2
Package 2 Height	50.000 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	66.500 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Recommended replacement(s)