

Product data sheet

Specifications



Easy UPS 1 Ph On-Line, 3kVA,
Tower, 230V, 6x IEC C13 + 1x IEC
C19 outlets, Intelligent Card Slot,
LCD, Extended runtime, No Battery

SRVSPM3KIL

Overview

Presentation	For small to medium businesses, Easy UPS 1 Ph On-Line provides essential power protection for unstable power conditions, ensuring consistent and reliable connectivity at the most critical moments.
Lead Time	Usually in Stock

Main

Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	2400 W
Rated Power In Va	3000 VA
Input Connection Type	IEC 60320 C20
Output Connection Type	6 IEC 60320 C13 1 IEC 60320 C19
Cable Length	1.52 m
Number Of Cables	1
Provided Equipment	1 IEC 60320 C19 to Schuko power cable 1 IEC 60320 C13 to C14 power cable 1 USB cable 1 RS-232 configuration cable 1 battery cable user manual

Batteries & Runtime

Efficiency	View Efficiency Graph
Battery Type	External battery system
Battery Voltage	72 V
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Charger Power	234 W rated

General

Number Of Power Module Filled Slots	0
-------------------------------------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Power Module Free Slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	23.8 cm
Width	14.5 cm
Depth	40.0 cm
Net Weight	7.9 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Usb Compatible	Yes
Mounting Position	Vertical

Input

Input Power Factor At Full Load	0.95
Input Voltage Limits	110...285 V half load 160...280 V full load
Network Frequency	40...70 Hz auto sensing

Output

Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2400 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Ups Type	Double conversion online
Wave Type	Sine wave
Efficiency	88 % (full load)
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass Type	Internal bypass (automatic and manual)
Crest Factor	3 : 1

Conformance

Product Certifications	CE UKCA
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 m

Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...15000 m
Acoustic Level	50 dBA
Heat Dissipation	910 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control Panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge Energy Rate	600 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33.0 cm
Package 1 Width	23.5 cm
Package 1 Length	47.7 cm
Package 1 Weight	9.6 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	7
Package 2 Height	45 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	69.3 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information