

Product data sheet

Specifications



solid state relay - DIN rail mount -
input 90-280 V AC, output 12-280 V
AC, 3A

SSLM1A13M7

⚠ Discontinued on: Sep 14, 2021

⚠ Discontinued

Main

Range Of Product	Harmony Relay
Product Or Component Type	Solid state relay
Device Short Name	SSLM
Network Number Of Phases	1 phase

Complementary

Mounting Support	Symmetrical DIN rail
[In] Rated Current	3 A
Output Voltage	12...280 V AC
[Uc] Control Circuit Voltage	90...280 V AC
Contacts Type And Configuration	1 NO
Clamping Force	0.6...0.8 N.m
Connections - Terminals	Screw terminals,clamping capacity: 1 x 0.2...1 x 5.26 mm² (AWG 24...AWG 10)
Switching Voltage	90 V AC turn-on
Load Current	0.1...3 A
Maximum Voltage Drop	<1.65 V on-state
Maximum Leakage Current	5 mA off-state
Overvoltage Category	III
Width	7.5 mm
Height	80 mm
Depth	63 mm
Net Weight	0.03 kg

Environment

Dielectric Strength	4000 V for input/output
Pollution Degree	2
Product Certifications	CSA UL EAC
Marking	EAC CSA UL CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...70 °C
---------------------------------------	-----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	0.75 cm
Package 1 Length	8 cm
Package 1 Weight	31 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free


✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings


Dimensions



(A) Fuse Holder

Connections and Schema

Wiring Diagram



- 1,2 : Field VAC (Supply through Load)
- 3,4 : Input
- (1) Load
- (2) Zero voltage detect
- (A) LED