

# Product data sheet

Specifications



single phase relay, Harmony Solid State Modular Relays, 6A, DIN rail mount, DC switching, input 4 to 32V DC, output 1 to 60V DC

SSM1D26BD

## Main

Range Of Product	Harmony Solid State Relays
Product Or Component Type	Solid state relay up to 10 A
Device Short Name	SSM
Number Of Channels	1
Number Of Phases	1 phase
Output Switching Mode	DC switching

## Complementary

Mounting Support	Symmetrical DIN rail
[In] Rated Current	6 A
Output Voltage	1...60 V DC
[Uc] Control Circuit Voltage	4...32 V DC
Tightening Torque	0.5...0.8 N.m for input 0.5...0.8 N.m for output
Connections - Terminals	Screw terminals: 1 x 0.3...1 x 1.5 mm², (AWG 22...AWG 16) for input Screw terminals: 1 x 0.3...1 x 2.5 mm², (AWG 22...AWG 14) for output
Maximum Capacitance	10 pF for input/output
Insulation Resistance	1000 MOhm at 500 V DC
Local Signalling	LED (green) for input status
Minimum Switching Voltage	4 V DC turn-on
Maximum Switching Voltage	1 V DC turn-off
Input Current	8...11 mA
Solid State Output Type	Mosfet output DC switching
Load Current	0.0025...6 A
Transient Overvoltage	60 V
Surge Current	60 A for 10 ms
Maximum Voltage Drop	<0.6 V on-state
Resistance	0.1 Ohm on-state
Maximum Leakage Current	0.1 mA off-state
Response Time	0.6 ms (turn-on) 0.3 ms (turn-off)
Overvoltage Category	III

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	11 mm
Height	90.3 mm
Depth	83.7 mm
Net Weight	0.05 kg

## Environment

Flame Retardance	V0 conforming to UL 94
Dielectric Strength	4 kV DC for input/output 4 kV DC for input or output to case
Pollution Degree	2
Standards	IEC 61000 IEC 62314 IEC 60950-1
Product Certifications	UL CSA
Marking	CE
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-30...80 °C
Ambient Air Temperature For Storage	-30...100 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	9 cm
Package 1 Length	9 cm
Package 1 Weight	61 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	96
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.26 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free


✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>


Dimensions Drawings

Dimensions



Performance Curves

Derating Curves



- A : Load Current (Amperes)  
B : Ambient Temperature (°C)  
1 : Multiple units, no minimum spacing between components  
2 : Installed single unit, distance to adjacent components more than 11 mm