


Product data sheet

Specifications



three phase relay, Harmony Solid State Relays, 50A, panel mount, zero voltage switching, input 180 to 280V AC, output 48 to 530V AC

SSP3A250P7

Main

Range Of Product	Harmony Solid State Relays
Product Or Component Type	Solid state relay up to 50 A
Device Short Name	SSP
Mounting Support	Panel
Number Of Phases	3 phases
[In] Rated Current	50 A
Solid State Output Type	Zero voltage switching
Output Switching Mode	Zero voltage switching

Complementary

Control Type	Without test button
Minimum Switching Voltage	180 V AC turn-on
Maximum Switching Voltage	10 V AC turn-off
Response Time	20 ms (turn-on) 30 ms (turn-off)
Input Current	7...20 mA
Load Current	0.1...50 A
Transient Overvoltage	1200 V
Surge Current	715 A for 20 ms 750 A for 16.6 ms 150 A for 1 s
Maximum I²T For Fusing	2520 A².s for 10 ms at 50 Hz 2320 A².s for 8.3 ms at 60 Hz
Maximum Leakage Current	3 mA off-state
Maximum Voltage Drop	<1.35 V on-state
Dv/Dt	500 V/µs off-state at maximum voltage
Power Factor	0.5 (with maximum load)
Motor Controller Rating	1.5 hp 40 °C 120 V AC 3 hp 40 °C 240 V AC 7.5 hp 40 °C 480 V AC 8.8 hp 40 °C 530 V AC
Motor Power Kw	1.11 kW at 40 °C 120 V AC 2.22 kW at 40 °C 240 V AC 5.55 kW at 40 °C 480 V AC 6.47 kW at 40 °C 530 V AC
Insulation Resistance	>= 1000 MOhm at 500 V DC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Capacitance	8 pF for input/output
Dielectric Strength	4 kV AC for input/output 4 kV AC for input or output to case
Tightening Torque	0.9...1.1 N.m for input 1.7...2.2 N.m for output
Connections - Terminals	Screw terminals: 1 x 0.2...1 x 2.5 mm², (AWG 24...AWG 14) for input Screw terminals: 1 x 1.5...1 x 10 mm², (AWG 16...AWG 8) for output
Thermal Resistance	0.12 °C/W
Led Indicator	LED, green for input
Ip Degree Of Protection	IP20
Net Weight	0.24 kg
Width	101.3 mm
Height	79.7 mm
Depth	35.4 mm
Device Presentation	Complete product

Environment

Flame Retardance	V0 conforming to UL 94
Ambient Air Temperature For Operation	-40...80 °C
Ambient Air Temperature For Storage	-40...125 °C
Pollution Degree	2
Overvoltage Category	III
Product Certifications	UL CSA
Marking	CE
Standards	IEC 60950-1 IEC 62314 IEC 61000

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	8.5 cm
Package 1 Length	12.0 cm
Package 1 Weight	278.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	27
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	11.588 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free


✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings


Dimensions



(1) 4 Mounting slots

Performance Curves

Derating Curves



A : Load Current (Amperes)
B : Ambient Temperature (°C)