

Product data sheet

Specifications



Symmetra PX 100kW Scalable to 100kW, 208V with Startup, No Battery

SY100K100F-NB

Overview

Presentation	A modular, high-efficiency 3-phase UPS that is scalable up to 100kW. Suitable for use in small to medium data centers and high density zones.
Lead Time	Usually Ships within 3 Weeks

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	120 V 208 V 208 V 3 phases
Rated Power In W	100000 W
Rated Power In Va	100000 VA
Output Connector Type	Hard wire 5-wire (3P + N + E) 1
Battery Type	External battery system
Provided Equipment	Installation guide Network management card Start-up service User manual

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Number Of Battery Free Slots	0
Extended Runtime	0

General

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	10
Redundant	Yes

Physical

Colour	Black
Height	201.1 cm
Width	60 cm
Depth	107 cm
Net Weight	571 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Usb Compatible	No
----------------	----

Input

Network Frequency	40...70 Hz
Input Voltage Limits	177...239 V 208 V
Maximum Input Current	332 A
Input Harmonic Distortion	Less than 5 % for full load
Load Power Factor	0.5 leading to 0.5 lagging
Input Power Factor At Full Load	0.99

Output

Maximum Configurable Power In W	100000 W 100000 W
Harmonic Distortion	Less than 2 %
Output Frequency	57...63 Hz for 60 Hz nominal sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Ups Type	Double conversion online
Wave Type	Sine wave
Output Voltage Tolerance	+/- 1% static and +/- 5% at 100% load step
Output Harmonic Distortion	< 2% for 0 to 100% linear load and < 6% for full non-linear load
Bypass Type	Built-in static bypass
Maximum Configurable Power In Va	100000 VA
Transfer Time	2 ms typical

Conformance

Standards	CSA C22.2 No 107.3-05 FCC part 15 class A ISO 14001 ISO 9001 UL 1778
-----------	--

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m
Acoustic Level	67 dBA
Nema Degree Of Protection	NEMA 1

Communications & Management

Free Slots	2
Preinstalled Device	Network management card with CAN

Control Panel	Multifunction LCD status and control console
---------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	214 cm
Package 1 Width	121 cm
Package 1 Length	84.8 cm
Package 1 Weight	298.87 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient

Resource performance

 Energy Efficient Product

Eu Rohs Directive

Not compliant