

Product data sheet

Specifications



Symmetra PX 160kW 400V w/ Integrated Modular Distribution

SY160K160H-PD

Overview

Presentation	A high-efficiency 3-phase UPS with integrated modular distribution that can be right-sized to your data center power requirements. With scalable power, distribution and run-time, this UPS grows with your data center up to 160kW/160kVA. Suitable for small to medium data centers or individual zones of large data centers.
Lead Time	Usually Ships within 3 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Rated Power In W	160000 W
Rated Power In Va	160000 VA
Output Connector Type	Hard wire 5-wire (3P + N + E) 1
Battery Type	VRLA
Provided Equipment	Network management card Start-up service User manual

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Number Of Battery Filled Slots	15
Number Of Battery Free Slots	3
Battery Recharge Time	3.5 h
Number Of Battery Replacement Quantity	4
Additional Information	Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage
Battery Voltage	+/- 192 V (split battery referenced to neutral)
Discharge Battery Voltage	+/- 154 V
Overcurrent Protection	945 A
Maximum Short-Circuit Current	10 kA
Max Current Discharge	550 A
Battery Overload Operation	10 minutes at 125% and 60 seconds at 150%
Battery Charger Power	14769 W rated
Battery Design Life	5...8 year(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Extended Runtime	1
------------------	---

General

Bypass Wiring Configuration	5 wire (3P + N + E)
Max Bypass Input Current	250 A
Bypass Current Protection	250 A
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	10
Redundant	Yes

Physical

Colour	Black
Height	199.1 cm
Width	180 cm
Depth	107 cm
Net Weight	2878 kg
Usb Compatible	No

Input

Network Frequency	40...70 Hz
Number Of Input Connectors	1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	340...477 V
Maximum Input Current	295 A
Switching Current Capacity	315 A
Max Short Time Withstand Current	30 kA
Input Harmonic Distortion	Less than 5 % for full load
Load Power Factor	0.5 leading to 0.5 lagging
Input Power Factor At Full Load	0.99

Output

Maximum Configurable Power In W	160000 W
Harmonic Distortion	Less than 2 %
Output Frequency	50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Ups Type	Double conversion online
Wave Type	Sine wave
Output Voltage Tolerance	+/- 1% static and +/- 5% at 100% load step
Output Harmonic Distortion	< 2% for 0 to 100% linear load and < 6% for full non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Required Output Current Protection	250 A
Neutral Output Current	400 A
Bypass Type	Built-in static bypass

Efficiency	94 % (in battery operation)
Maximum Configurable Power In Va	160000 VA

Conformance

Product Certifications	EUROBAT
Standards	EN 50091-1 EN/IEC 62040-1-1 EN/IEC 62040-2 EN/IEC 62040-3 ISO 14001 ISO 9001 VFI-SS-111

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m
Acoustic Level	63 dBA
Heat Dissipation	28741 Btu/h
Nema Degree Of Protection	NEMA 1
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	2
Preinstalled Device	Network management card with CAN
Control Panel	Multifunction LCD status and control console
Emergency Power Off	Yes

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	214 cm
Package 1 Width	121 cm
Package 1 Length	223.5 cm
Package 1 Weight	3116 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient

Resource performance

 Energy Efficient Product

Eu Rohs Directive

Under investigation