

# Product data sheet

Specifications



## APC Symmetra LX 8kVA Scalable to 16kVA N+1 Ext. Run Tower, 220/230/240V or 380/400/415V

SYA8K16IXR

### Overview

Presentation	High performance, redundant power protection with scalable power and runtime for space-constrained server rooms, and voice and data networks.
Lead Time	Usually in Stock

### Main

Main Input Voltage	230 V 400 V 3 phases
Other Input Voltage	220 V 240 V 380 V 415 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	5600 W
Rated Power In Va	8000 VA
Output Connector Type	Hard wire 3-wire (H N + E) 1
Battery Type	Lead-acid battery
Provided Equipment	CD with software Documentation CD User manual Web/SNMP management card

### Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Number Of Battery Filled Slots	9
Number Of Battery Free Slots	4
Battery Recharge Time	7.5 h
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage
Battery Charger Power	1035 W rated
Battery Life	3...5 year(s)
Extended Runtime	1

### General

Product Web Sub-Family	4kVA power increments
------------------------	-----------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Power Module Free Slots	3
Number Of Power Module Filled Slots	2
Redundant	Yes

## Physical

Colour	Black Silver
Height	151.6 cm
Width	48.3 cm
Depth	72.6 cm
Net Weight	473.64 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

## Input

Network Frequency	45...65 Hz auto-sensing
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E) 1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	155...276 V 1:1 290...480 V 3:1
Input Harmonic Distortion	Less than 7 % for full load
Input Power Factor At Full Load	0.98

## Output

Maximum Configurable Power In W	11200 W
Harmonic Distortion	Less than 5 % at full load
Output Frequency	47...63 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest Factor	Up to 5 : 1
Ups Type	Double conversion online
Wave Type	Sine wave
Bypass Type	Internal bypass (automatic and manual)
Maximum Output Current	36 A
Maximum Configurable Power In Va	16000 VA

## Conformance

Product Certifications	C-Tick CE GOST VDE
------------------------	-----------------------------

Standards	EN 50091-1 EN 50091-2 EN 55022 class A EN 55024 EN 60950 IEC 60950
-----------	---

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...4572.00 m
Acoustic Level	62 dBA
Heat Dissipation	3707 Btu/h

## Communications & Management

Free Slots	1
Preinstalled Device	Network management card 2 with environmental monitoring
Control Panel	Multifunction LCD status and control console
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	188 cm
Package 1 Width	99.7 cm
Package 1 Length	59.9 cm
Package 1 Weight	502.27 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient   Take-back   RoHS/REACH

## Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins