

Product data sheet

Specifications



Symmetra PX Power Module, 10/16kW, 400V

SYPM10K16H

Overview

Presentation	A 16kW high efficiency power module for the Symmetra PX160kW & PX48kW. This power module is backward compatible with the SYPM10KH module and will autotetect to deliver only 10kW of power protection if installed in a PX80kW, 40KW or 20kW all-in-one.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Rated Power In W	16000 W
Rated Power In Va	16000 VA
Output Connector Type	Hard wire 5-wire (3P + N + E) 1
Provided Equipment	Installation guide

Batteries & Runtime

Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Additional Information	Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage

Physical

Height	13.2 cm
Width	48.3 cm
Depth	70 cm
Net Weight	28.5 kg
Mounting Location	Front
Usb Compatible	No

Input

Network Frequency	40...70 Hz
Number Of Input Connectors	1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	340...477 V
Maximum Input Current	33 A
Max Short Time Withstand Current	30 kA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input Harmonic Distortion	Less than 5 % for full load
Input Power Factor At Full Load	0.99

Output

Maximum Configurable Power In W	16000 W
Harmonic Distortion	Less than 2 %
Output Frequency	50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest Factor	Unlimited
Ups Type	Double conversion online
Output Voltage Tolerance	+/- 1% static and +/- 5% at 100% load step
Output Harmonic Distortion	< 2% for 0 to 100% linear load and < 6% for full non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%

Conformance

Product Certifications	CE
Standards	EN 50091-1 EN 50091-3 FCC part 15 class A VFI-SS-111

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...4572.00 m
Acoustic Level	63 dBA
Heat Dissipation	2573 Btu/h
Nema Degree Of Protection	NEMA 1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.5 cm
Package 1 Width	70 cm
Package 1 Length	59.5 cm
Package 1 Weight	31.55 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

<div><div><div>✓</div></div></div> <div>Rohs Exemption Information</div>	<div>Yes</div>
<hr/>	
Eu Rohs Directive	Compliant with Exemptions
<hr/>	
China Rohs Regulation	<div><div>China RoHS declaration</div><div>Product out of China RoHS scope. Substance declaration for your information</div></div>
<hr/>	
Environmental Disclosure	<div>Product Environmental Profile</div>
<hr/>	
Circularity Profile	<div>End of Life Information</div>
<hr/>	