

# Product data sheet

Specifications



Miniature circuit breaker (MCB),  
Multi9 C60BP, 3P, 20A, C curve,  
10kA (UL489), 10kA (IEC/EN  
60947-2)

M9F42320

## Main

Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60BP
Device Application	Distribution
Poles Description	3P
Number Of Protected Poles	3
[In] Rated Current	20 A at 25 °C conforming to EN/IEC 60947-2
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	6 kA Icu at 440 V AC conforming to EN/IEC 60947-2 10 kA Icu at 415 V AC conforming to EN/IEC 60947-2 20 kA Icu at 240 V AC conforming to EN/IEC 60947-2 6 kA Icu at 440 V AC conforming to GB 14048.2 10 kA Icu at 415 V AC conforming to GB 14048.2 20 kA Icu at 240 V AC conforming to GB 14048.2 14 kA AIR at 240 V AC conforming to UL 489 10 kA AIR at 480Y/277 V AC conforming to UL 489 14 kA AIR at 240 V AC conforming to CSA C22.2 No 5 10 kA AIR at 480Y/277 V AC conforming to CSA C22.2 No 5
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Standards	EN/IEC 60947-2 GB 14048.2 UL 489 CSA C22.2 No 5
Product Certifications	IEC CCC CSA UL

## Complementary

[Ue] Rated Operational Voltage	240 V AC 50/60 Hz 415 V AC 50/60 Hz 440 V AC 50/60 Hz
Magnetic Tripping Limit	8.5 x In +/- 20 % AC
[Ics] Rated Service Breaking Capacity	4.5 kA 75 % conforming to EN/IEC 60947-2 - 440 V AC 7.5 kA 75 % conforming to EN/IEC 60947-2 - 415 V AC 15 kA 75 % conforming to EN/IEC 60947-2 - 240 V AC 4.5 kA 75 % conforming to GB 14048.2 - 440 V AC 7.5 kA 75 % conforming to GB 14048.2 - 415 V AC 15 kA 75 % conforming to GB 14048.2 - 240 V AC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ui] Rated Insulation Voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	6
Height	103 mm
Width	54 mm
Depth	72 mm
Colour	Grey
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Tunnel type terminal (top or bottom)1...25 mm² (AWG 18...AWG 8) - rigid Tunnel type terminal (top or bottom)1...16 mm² (AWG 18...AWG 8) - flexible with ferrule Tunnel type terminal (top or bottom)1...16 mm² (AWG 18...AWG 8) - flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2.5 N.m top or bottom
Earth-Leakage Protection	Without

## Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	0...2000 m
Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...80 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	5.400 cm
Package 1 Length	10.300 cm
Package 1 Weight	372.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	8.300 cm

Package 2 Width	10.800 cm
Package 2 Length	22.000 cm
Package 2 Weight	1.530 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	14.363 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations