

# Product data sheet

Specifications



## EASYLOGIC DM6200H VAF PF DPM RS48 CL1.0

METSEDM6200HCL10RS

### Main

Range	EasyLogic
Product Name	EasyLogic DM6X00H RS
Device Short Name	DM6200H
Product Or Component Type	VAF PF meter

### Complementary

Device Application	Remote monitoring
Type Of Measurement	Current Voltage Frequency RPM
Metering Type	Unbalance current Rotation speed Average current Iavg Average voltage Vavg Unbalance voltage Phase currents Frequency Calculated neutral current Voltage U21, U32, U13, V1, V2, V3
Counter Functions	ON hour counting Power interruption
[Us] Rated Supply Voltage	48...277 V AC 45...65 Hz 48...277 V DC
Network Frequency	60 Hz 50 Hz
[In] Rated Current	1 A 5 A
Type Of Network	3P + N 3P 1P + N 2P + N 2P
Maximum Power Consumption In Va	4 VA at 240 V between phase and neutral
Maximum Power Consumption In W	2 W at 240 V
Display Type	8 segments LED
Display Colour	Red
Messages Display Capacity	3 fields of 4 characters
Display Digits	12 digit(s) - 14.2 mm in height

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Communication Of Data	Instantaneous and demand values Revolution speed All counters Reading of measurements
Tamperproof Of Settings	Protected by access code
Sampling Rate	32 samples/cycle
Measurement Current	5...6000 mA
Signal	Current 0.005...10 A (impedance 0.3 MOhm)6 x
Measurement Voltage	46...277 V AC 50...60 Hz between phase and neutral 80...480 V AC 50...60 Hz between phases 277...999000 V AC 50...60 Hz with external VT
Frequency Measurement Range	45...65 Hz
Number Of Inputs	2
Measurement Accuracy	Frequency +/- 0.05 % Power factor +/- 0.01 Current +/- 1 % Voltage +/- 1 %
Accuracy Class	Class 1
Demand Intervals	1 s
Local Signalling	Green LED: activity Red LED: output signal 1...9999000 pulse/ k_h (kWh, kVAh, kVARh)
Communication Port Protocol	Modbus at 4800 bps, 9600 bps, 19200 bps, 38.4 Kbps even/odd or none - 2-wire, insulation 2500 V
Communication Port Support	Screw terminal block: RS485
Material	Polycarbonate
Flame Retardance	V-0 conforming to UL 94
Mounting Mode	Flush-mounted
Mounting Support	Framework
Installation Category	III
Type Of Installation	Indoor installation
Measurement Category	Category III 480 V
Electrical Insulation Class	Class II
Connections - Terminals	Current circuit: screw clamp terminals (bottom) 2.08...3.31 mm <sup>2</sup> cable(s) Voltage circuit: screw clamp terminals (top) 0.82...3.31 mm <sup>2</sup> cable(s) Control circuit: screw clamp terminals (top) 0.82...3.31 mm <sup>2</sup> cable(s) Communication: screw clamp terminals (bottom) 0.33...3.31 mm <sup>2</sup> cable(s)
Tightening Torque	Current circuit: 0.9...1 N.m Philips No 2 screwdriver Voltage circuit: 0.9...1 N.m Philips No 2 screwdriver Control circuit: 0.9...1 N.m Philips No 2 screwdriver Communication: 0.5...0.6 N.m Philips no 1 screwdriver
Wire Stripping Length	Current circuit: 3.68 mm Voltage circuit: 7 mm Control circuit: 7 mm Communication: 7 mm
Standards	IEC 61010-1:ed. 3 UL 61010-1:ed. 3
Product Certifications	CE conforming to IEC 61010-1 CULus conforming to UL 61010-1 CULus conforming to CSA C22.2 No 61010-1 C-Tick
Width	96 mm

Depth	13 mm outside: 49 mm panel:
Height	96 mm
Net Weight	300 g

## Environment

Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Surge immunity test conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Magnetic field at power frequency conforming to IEC 61000-4-8 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Emission tests conforming to FCC part 15 class A Emission tests conforming to FCC part 15 Subpart C Emission tests conforming to FCC part 15 Subpart E
Overvoltage Category	III
Ip Degree Of Protection	IP51 front: conforming to IEC 60529 IP30 body: conforming to IEC 60529
Relative Humidity	5...95 % at 50 °C
Pollution Degree	2
Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-20...70 °C
Operating Altitude	<= 2000 m
Service Life	7 year(s)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.905 cm
Package 1 Width	11.903 cm
Package 1 Length	12.229 cm
Package 1 Weight	360 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6480 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	133.5 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>